



KPB4CG1, Copper Alloy Clip-on, Lay-in Ground Connector

By Burndy
Catalog # [KPB4CG1](#)

Copper Alloy Clip-on/Lay-in Ground Connector, Accommodates #10 - #4 CU

Features

- UL467 Listed for Direct Burial in earth or concrete
- UL486 Listed
- Exclusive design accommodates #10-#4 Copper where continuous conductor runs are preferable

Application

For Direct Burial In Earth Or Concrete

Specifications

Standards - Industry Standards Met	• UL467 • UL 486A-B
Standards - RoHS Compliance Status	CM
Buy American Compliant	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • UL 486A-B
UL Listed	Yes

Conductor

Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG

- 4 AWG

Dimensions

Package Height	0.000 in
Dimension - Height inch	0.95 in
Package Weight	0.000 lb.
Dimension - Width inch	0.99 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.61 in
Dimension - Width fraction	1 in

Force Related

Installation Torque Recommended in-lb	45 LBS/in
---------------------------------------	-----------

General

Plated	No
Sub Brand	SCRULUG
Product Type	Mechanical
UPC	781810100233
Type	KPB
Material Type - Screw	Steel - Stainless
Material	Copper Alloy
Plating Type	Tin
UPC 12 Digit	781810100233
UPC 14 Digit GTIN	00781810100233

Logistics

Minimum Pack Quantity	1
Pallet Quantity	39600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)