



KPU2929T, Connector Only, Insulated Gutter Tap

By Burndy
Catalog # [KPU2929T](#)

Connector Only, 1/0 AWG-250 kcmil Run, #6 AWG-250 kcmil Tap, AL/Cu, KPU3C Red Cover available separately



Features

- 600 Volt Rated
- AL9CU dual rated for use with aluminum or copper conductor
- UL Listed to UL486A-B, CSA Certified to C22.2 No. 65
- Manufactured from high strength 6061-T6 aluminum alloy
- Electro tin plated for low contact resistance and protection against corrosion
- Tap parallel or perpendicular to run conductor
- Connectors are re-useable

Conductor

Conductor - AL Str Run Range	1/0 AWG - 250 kcmil
Conductor - AL Str Tap Range	6 AWG - 250 kcmil
Conductor - Copper Str Run Range	1/0 AWG - 250 kcmil

Conductor - Copper Str Tap Range	6 AWG - 250 kcmil
----------------------------------	-------------------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	621945657540
-----	--------------

Product Assets

[Catalog \[English\]](#)