



KS28, Split Bolt Connector, Run/Tap: #1-4/0 AWG

By Burndy
Catalog # [KS28](#)

Copper Split Bolt, Cu: 1-4/0 AWG (Run & Tap)



Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL 486A • UL486B
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL 486A • UL486B
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Run Range	1 STR - 4/0 STR
Conductor - Copper Str Run	• 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Run Range	1 AWG - 4/0 AWG
Conductor - Copper Solid Run	• 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Tap Range	1 AWG - 4/0 AWG
Conductor - Copper Solid Tap	• 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor Type	• CU C Solid-Run

- CU C Str-Run
- CU Weld C Solid-Run
- CU Weld C Str-Run
- CU C Str-Tap
- CU Weld C Solid-Tap
- CU Weld C Str-Tap
- CU C Solid-Tap

1 STR - 4/0 STR

Conductor - Copper Str Tap Range

Conductor - Copper Str Tap

- 1 AWG
- 1/0
- 2/0 AWG
- 3/0 AWG
- 4/0 AWG

Configuration

Connector Type Split Bolt

Dimensions

Package Height	0.000 in
Length	2.46 in
Package Weight	0.000 lb.
Dimension - Width mm	30 mm
Dimension - Width inch	1.17 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	53 mm
Height	1.35 in
Width	1.18 in
Dimension - Length Overall inch	2.46
Dimensions	2.46 in x 1.18 in x 1.35 in

Force Related


Installation Torque Recommended in-lb 650 in

General

Plated	N
Trade Name	SERVIT®
UPC	781810422007
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810422007

Logistics

Pallet Quantity3600



Product Assets

[Catalog \[English\]](#)