



KS34, Split Bolt Connector, Run/Tap: 2/0 AWG Str-500 kcmil

By Burndy
Catalog # [KS34](#)

Copper Split Bolt, Cu: 2/0 AWG (Str)-500 kcmil (Run & Tap).



Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

Application

For Direct Burial Cables

Specifications

Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run
----------------	---

- CU C Str-Tap
- CU Weld C Solid-Tap
- CU Weld C Str-Tap
- CU C Solid-Tap

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	781810014509
Type	KS
Material	Copper
UPC 12 Digit	781810014509

Logistics

Pallet Quantity	1
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)