



KSSB39U, QIKSHEAR™ Series, Shear Bolt Splice, 600-750 kcmil

By Burndy
Catalog # [KSSB39U](#)

Mechanical Shear Bolt Splice, 600-750 kcmil, Cu/Al, Tin Plated Connector and Screws, 3/8" Hex Key

Features

- No Tooling or Die Investment Required, no crimp tools necessary
- Dual Rated AL9CU for use with both copper and aluminum conductor
- cULus Listed Wire Connector to UL486A-486B
- Up to 35kV voltage rating
- Tin Plated aluminum connectors and bolts reduce galvanic corrosion and oxide build up
- Range-taking capabilities on most sizes

Dimensions

Package Height	0.000 in
Length	7 in



Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	621945658936
Series	QIKSHEAR™ Series

Logistics

Carton Quantity	20
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)