



KSSB44U, QIKSHEAR™ Series, Shear Bolt Splice, 1000 kcmil

By Burndy
Catalog # [KSSB44U](#)

Mechanical Shear Bolt Splice, 1000 kcmil, Cu/Al, Tin Plated Connector and Screws, 3/8" Hex Key



Features

- No Tooling or Die Investment Required, no crimp tools necessary
- Dual Rated AL9CU for use with both copper and aluminum conductor
- cULus Listed Wire Connector to UL486A-486B
- Up to 35kV voltage rating
- Tin Plated aluminum connectors and bolts reduce galvanic corrosion and oxide build up
- Range-taking capabilities on most sizes

Conductor

Wire Range 1000 kcmil (Class B & C)

Dimensions

Package Height 0.000 in
Length 7 in

Package Weight	0.000 lb.
Package Length	0.000 in
Outside Diameter	2.01
Package Width	0.000 in
General	
UPC	621945638532
Hex Key	3/8"
Series	QIKSHEAR™ Series

Logistics

Pallet Quantity 450
Carton Quantity 5

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)