



KSSB45U, QIKSHEAR™ Series, Shear Bolt Splice, 1250 kcmil

By Burndy
Catalog # [KSSB45U](#)

Mechanical Shear Bolt Splice, 1250 kcmil, Cu/Al, Tin Plated
Connector and Screws, 3/8" Hex Key

Features

- No Tooling or Die Investment Required, no crimp tools necessary
- Dual Rated AL9CU for use with both copper and aluminum conductor
- cULus Listed Wire Connector to UL486A-486B
- Up to 35kV voltage rating
- Tin Plated aluminum connectors and bolts reduce galvanic corrosion and oxide build up
- Range-taking capabilities on most sizes

Dimensions



Package Height	0.000 in
Length	7.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
General	
UPC	621945658943
Series	QIKSHEAR™ Series

Product Assets

[Catalog \[English\]](#)