



KSU22, Split Bolt Connector with Spacer, Tin Plated

By Burndy

Catalog # [KSU22](#)

Tin plated copper alloy SERVIT with spacer to separate dissimilar conductors

Features

- Tin-plated, high strength copper alloy with spacer
- Spacer separates dissimilar conductors and provides long contact length preventing high pressure point contacts between run and tap conductors

Application

For All Combinations Of Copper, Aluminum, ACSR, AAAC, 5005, And Steel

Specifications

Buy American Compliant	Yes
EU RoHS Indicator	Yes
Buy America(n) Qualified	• Buy America Compliant (All status valid till December 2025) • Buy American Act Compliant (All status valid till December 2025) • BABA Compliant (All status valid till December 2025)
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor - Galvanized Steel Str Size	1/4 (7) in
Conductor - Galvanized Steel Str Size Range	1/4 (7) in
Conductor - AAAC 5005 Tap	• 30.58 (7) kcmil • 48.69 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil-48.69 (7) kcmil
Conductor - AAAC 6201 Run	• 30.58 (7) kcmil • 48.69 (7) kcmil
Conductor - AAAC 6201 Run Range	30.58 (7) kcmil-48.69 (7) kcmil
Conductor - AAAC 6201 Tap	• 30.58 (7) kcmil • 48.69 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil-48.69 (7) kcmil
Conductor - ACSR Str Run	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG



Conductor - ACSR Str Run Range	• 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG 6 AWG - 4 AWG
Conductor - ACSR Str Tap	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG 6 AWG - 4 AWG
Conductor - ACSR Str Tap Range	
Conductor - AL Str Run	• 10 AWG • 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - AL Str Run Range	10 STR. - 2 SOL.
Conductor - AL Str Tap	• 10 AWG • 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - AL Str Tap Range	10 STR. - 2 SOL.
Conductor - Copper Solid Run	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Solid Run Range	10 AWG-2 AWG
Conductor - Copper Solid Tap	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Solid Tap Range	10 AWG-2 AWG
Conductor - Copper Str Run	• 10 AWG

	• 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Str Run Range	10 STR. - 2 SOL.
Conductor - Copper Str Tap	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Str Tap Range	10 STR. - 2 SOL.
Conductor Type	• CU C Solid-Run • CU C Str-Run • AL C Str-Run • AAAC C 5005-Run • AAAC C 6201-Run • ACSR C Str-Run • CU C Solid-Tap • CU C Str-Tap • AL C Str-Tap • AAAC C 5005-Tap • AAAC C 6201-Tap • ACSR C Str-Tap • GAL Steel C Str-Size
Conductor - AAAC 5005 Run	• 30.58 (7) kcmil • 48.69 (7) kcmil
Conductor - AAAC 5005 Run Range	30.58 (7) kcmil-48.69 (7) kcmil

Connector Type

Split Bolt

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	32 mm
Package Height	0.000 in
Width	0.57 in
Dimension - Width inch	0.57 in
Dimension - Width mm	14 mm
Dimension - Length Overall inch	1.46
Dimension - Cross Flats inch	.74 in

Force Related

Installation Torque	275
Recommended in-lb	

General

Trade Name	SERVIT®
Sub Brand	UNIVERSAL SERVIT
Plated	Y
Type	KSU, Universal
UPC 12 Digit	781810035757
UPC 14 Digit GTIN	00781810035757
Material	Copper
Plating Type	Tin Plated
UPC	781810035757

Logistics

Minimum Pack Quantity	1
Carton Quantity	100
Pallet Quantity	17400

Product Assets

[Catalog \[English\]](#)

Configuration



A Hubbell brand