



KSU25G4, Split Bolt Connector with Spacer

By Burndy
Catalog # [KSU25G4](#)

Cu Alloy Universal SERVIT, Unplated-Autoline, #2 Str. Cu/Al, #3 AWG ACSR(Run), #10 Str. Cu/Al, #6 AWG ACSR(Tap)

Features

- Tin-plated, high strength copper alloy with spacer
- Spacer separates dissimilar conductors and provides long contact length preventing high pressure point contacts between run and tap conductors

- ACSR C Str-Tap
- GAL Steel C Str-Size

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor Type	• CU C Solid-Run • CU C Str-Run • AL C Str-Run • AAAC C 5005-Run • AAAC C 6201-Run • ACSR C Str-Run • CU C Solid-Tap • CU C Str-Tap • AL C Str-Tap • AAAC C 5005-Tap • AAAC C 6201-Tap
----------------	--

Configuration

Connector Type	Split Bolt
----------------	------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in

General

Trade Name	SERVIT®
Plated	Y
UPC 12 Digit	781810339695
UPC 14 Digit GTIN	00781810339695
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810339695

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)