



KSU25NK, Split Bolt Connector with Spacer, Nickel Plated

By Burndy
Catalog # [KSU25NK](#)

Cu Alloy Universal SERVIT, #2 Str. Cu/Al, #3 AWG ACSR(Run), #10 Str. Cu/Al, #6 AWG ACSR(Tap), Nickel Plated

Features

- Nickel-plated, high strength copper alloy with spacer
- Spacer separates dissimilar conductors and provides long contact length preventing high pressure point contacts between run and tap conductors

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor - Copper Str Run Range	2 AWG - 1/0 AWG
Conductor - Copper Str Tap Range	10 AWG - 1/0 AWG
Conductor - ACSR Str Run Range	3 AWG - 1AWG
Conductor - ACSR Str Tap Range	6 AWG - 1 AWG
Conductor - AL Str Run Range	2 AWG - 1/0 AWG
Conductor - AL Str Tap Range	10 AWG - 1/0 AWG

Configuration

Connector Type	Split Bolt
----------------	------------

Dimensions

Dimension - Length Overall	1.77
inch	
Width	0.7 in

General

Trade Name	SERVIT®
Plated	Y
UPC 12 Digit	781810239025
UPC 14 Digit GTIN	00781810239025
Material	Copper
Plating Type	Nickel
UPC	781810239025

Logistics

Minimum Pack Quantity	1
Carton Quantity	50
Pallet Quantity	23200

Product Assets

[Catalog \[English\]](#)