

KVS26, 2-piece OKLIP Service Connector for heavy duty applications

By Burndy
Catalog # [KVS26](#)



Compact 2-piece, high strength, copper alloy with neoprene rings

Features

- Compact, 2-piece, high strength, high copper alloy, recommended for heavy duty connections
- Neoprene rings hold silicon bronze bolts in place during installation
- Installed with ordinary wrench

Application

For Copper, Copperweld

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	RUS
Certification - ETL	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	1 str. 2/0 str.
Conductor - Copper Solid Tap Range	6 AWG-2/0 AWG
Conductor - Copper Solid Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - CopperWeld Solid Tap	3/0
Conductor - CopperWeld Solid Run	3/0
Conductor Type	• CU C Str-Run • CU C Str-Tap • CU Weld C Solid-Run

Conductor - Copper Str Tap Range	• CU Weld C Solid-Tap 6 str. - 2/0 str.
----------------------------------	---

Dimensions

Dimension - Pad Width inch	1.06 in
Package Height	0.000 in
Dimension - Height mm	44.20 mm
Dimension - Height inch	1.74 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Stud Size inch	5/16 in
Dimension - Width mm	40 mm
Dimension - Width inch	1.56 in

Force Related

Installation Torque Recommended in-lb	180 LBS/in
---------------------------------------	------------

General

Product Family	Power Connectors>Split Bolts>KVS
Trade Name	OKLIP™
Plated	No
Sub Brand	OKLIP
Product Type	Mechanical
UPC	781810061206
Type	KVS, Compact
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810061206
UPC 14 Digit GTIN	00781810061206

Logistics

Minimum Pack Quantity	1
Pallet Quantity	6000
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)