



KVS28G6, 2-piece OKLIP Service Connector for heavy duty applications, Run: 1/0-4/0 AWG Str, Tap: #10-4/0 AWG Str

By Burndy
Catalog # [KVS28G6](#)

Cast Cu Alloy Mechanical Service Connector, 1/0 - 4/0 AWG STR (Run), #10 - 4/0 AWG STR (Tap)

Features

- Compact, 2-piece, high strength, high copper alloy, recommended for heavy duty connections
- Neoprene rings hold silicon bronze bolts in place during installation
- Installed with ordinary wrench

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL486C
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Str-Run • CU C Str-Tap • CU Weld C Solid-Run • CU Weld C Solid-Tap
----------------	---

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
Trade Name	OKLIP™
UPC	781810145098
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810145098
UPC 14 Digit GTIN	00781810145098

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4500
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)