



KVS34G17, 2-piece OKLIP Service Connector for heavy duty applications

By Burndy
Catalog # [KVS34G17](#)



Cast Cu Alloy Service Connector, 400 - 500 kcmil(run), #10 str. - 500 kcmil(Tap)

Features

- High conductivity, non-copper bearing aluminum alloy connector with thick spacer and aluminum hardware
- Recommended for heavy duty dissimilar metal applications
- Spacer separates conductors and provides long contact length
- Longer peened bolt permits swivel action for easier installation
- Neoprene ring prevents loss of shorter bolt

- CU Weld C Solid-Run
- CU Weld C Solid-Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
Trade Name	OKLIP™
UPC	781810110935
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810110935
UPC 14 Digit GTIN	00781810110935

Logistics

Pallet Quantity	2688
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL486C
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Str-Run • CU C Str-Tap
----------------	---



A Hubbell brand