



KVS40AS, 2-piece OKLIP Service Connector for heavy duty applications

By Burndy
Catalog # [KVS40AS](#)

Cast Al Alloy Mechanical OKLIP, 400 - 800 kcmil Cu/AAC,338.4 - 715.5 kcmil Al/ACSR(Run), 3/0 Str. - 800 kcmil Cu/AAC, 3/0 AWG - 715.5 kcmil Al/ACSR(Tap)

Features

- High conductivity, non-copper bearing aluminum alloy connector with thick spacer and aluminum hardware
- Recommended for heavy duty dissimilar metal applications
- Spacer separates conductors and provides long contact length
- Longer peened bolt permits swivel action for easier installation
- Neoprene ring prevents loss of shorter bolt

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Type	• AL C Str-Run • CU C Str-Run • ACSR C Cmpt-Run • AAAC C 5005-Run • AAAC C 6201-Run • AL C Str-Tap • CU C Str-Tap
----------------	---



- ACSR C Cmpt-Tap
- AAAC C 5005-Tap
- AAAC C 6201-Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
Trade Name	OKLIP™
UPC	781810125908
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810125908
UPC 14 Digit GTIN	00781810125908

Logistics

Minimum Pack Quantity	16
Pallet Quantity	216
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)