



KVSU34CG1, Mechanical Connector with Spacer Bar

By Burndy
Catalog # [KVSU34CG1](#)

Mechanical connector



Features

- Compact, tin-plated high strength copper alloy connector with spacer and tin-plated silicon bronze hardware
- Recommended for heavy duty connections
- Spacer separates dissimilar conductors and provides long contact length
- Neoprene ring prevents loss of shorter bolt during installation
- Longer peened bolt permits swivel action for easier installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• AL C Str-Run • CU C Str-Run • AAAC C 5005-Run • AAAC C 6201-Run • ACSR C Str-Run • CU C Solid-Run • AL C Str-Tap • CU C Str-Tap • AAAC C 5005-Tap
----------------	---

- AAAC C 6201-Tap
- ACSR C Str-Tap
- CU C Solid-Tap
- GAL Steel C Str-Size

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	Y
Trade Name	OKLIP™
UPC	781810421994
Material	Copper Alloy
Plating Type	Tin
UPC 12 Digit	781810421994
UPC 14 Digit GTIN	00781810421994

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand