



KVSW26, Mechanical Connector with Spacer Bar

By Burndy
Catalog # [KVSW26](#)

Mechanical Connector For CUWeld and Copper Supplied with a
CU alloy Spacer that separates run and tap conductors, Run: 2
str. - 2/0 str., Tap:6 sol. - 2/0 str.

Features

- Compact, 2-piece, high strength, high copper alloy, recommended for heavy duty connections
- High copper alloy spacer bar separates run and tap conductors
- Provides high contact pressure, confines conductor strands and assures vibration-proof connection
- Longer peened bolt permits swivel action for easier installation
- Neoprene rings hold silicon bronze bolts in place during installation
- Installed with ordinary wrench

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	2 str. - 2/0 str.
Conductor - Copper Str Run	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-2/0 AWG
Conductor - Copper Solid Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Tap Range	6 sol. - 2/0 str.



Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG
----------------------------	---

Dimensions

Package Height	0.000 in
Dimension - Height mm	44.70 mm
Dimension - Height inch	1.76 in
Package Weight	0.000 lb.
Dimension - Width inch	1.56 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall inch	1.04 in
Dimension - Stud Size inch	5/16 in

Force Related

Installation Torque Recommended in-lb	180 LBS/in
---------------------------------------	------------

General

Plated	N
Trade Name	OKLIP™
UPC	781810065457
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810065457
UPC 14 Digit GTIN	00781810065457

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5824
Carton Quantity	13

Product Assets

[Catalog \[English\]](#)



A Hubbell brand