



LYM25C, MOLIMITER Replaceable Link, With DURICOMP™ Series, Shell and Rubber Sleeve for Insulated Cables.

By Burndy
Catalog # [LYM25C](#)

With DURICOMP™ Shell and Rubber Sleeve for Insulated Cables.



Features

- Replaceable Link MOLIMITER with Ceramic Shell and Rubber Sleeve for Insulated Cables
- The MOLIMITER is used to fuse underground cables at junction points with the Burndy MOLE
- The LYM Replaceable Link permits the selection of one of several link sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	UI
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	
Conductor - Copper Str Size	1/0 AWG

Configuration

Connector Type	Limiter
----------------	---------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	.75 in
Dimension - Length Overall	14.25 in
inch	

General

Plated	Y
Insulation Type	Diatex
Trade Name	MOLIMITER™
Die Index	99
UPC	781810000731
Insulation	Y
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810000731
UPC 14 Digit GTIN	00781810000731

Logistics

Minimum Pack Quantity	1
Pallet Quantity	384
Carton Quantity	4

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)