



LYM31C, MOLIMITER Replaceable Link

By Burndy
Catalog # [LYM31C](#)

BURNDY® MOLIMITER™ Replaceable Link



Features

- Replaceable Link MOLIMITER with Ceramic Shell and Rubber Sleeve for Insulated Cables
- The MOLIMITER is used to fuse underground cables at junction points with the Burndy MOLE
- The LYM Replaceable Link permits the selection of one of several link sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	UI
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	350 kcmil
Conductor - AL Str Size Range	350 kcmil
Conductor - Copper Str Size	350 kcmil
Range	
Conductor - Copper Str Size	350 kcmil

Configuration

Connector Type	Limiter
----------------	---------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.25 in
Dimension - Length Overall	14.25 in
inch	

General

Plated	Y
Insulation Type	Diatex
Trade Name	MOLIMITER™
Die Index	18
UPC	781810000793
Insulation	Y
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810000793
UPC 14 Digit GTIN	00781810000793

Logistics

Minimum Pack Quantity	1
Pallet Quantity	384
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)