



LYM34C, Replaceable Link Limiter - Cable To Mole

By Burndy
Catalog # [LYM34C](#)

Molimiter Replaceable Link, 500 KCMIL, Tin Plated, 20 Index



Features

- Replaceable Link MOLIMITER with Ceramic Shell and Rubber Sleeve for Insulated Cables
- The MOLIMITER is used to fuse underground cables at junction points with the Burndy MOLE
- The LYM Replaceable Link permits the selection of one of several link sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil
Range	
Conductor - Copper Str Size	500 kcmil

Configuration

Connector Type	Limiter
----------------	---------

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Length Overall	14.25 in
inch	

General

Feature - Barrel Style	Tapered
Plated	Y
Trade Name	MOLIMITER™
Die Index	20
UPC	781810000809
Insulation	Y
Material	Copper Alloy
Plating Type	Tin
UPC 12 Digit	781810000809
UPC 14 Digit GTIN	00781810000809

Logistics

Minimum Pack Quantity	12
Pallet Quantity	576
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)