



LYS29C, Replaceable Link Limiter - Cable To Cable

By Burndy
Catalog # [LYS29C](#)



Limiter Replaceable Link, 250 KCMIL, Tin plated, 16 Index

Features

- Type LYS Replaceable Link Limiter incorporates the functions of both fuse and coupler
- For use with rubber and paper-insulated cable, it is designed to facilitate rapid replacement of Limiter Links upon clearing

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	250 kcmil
Conductor - AL Str Size Range	250 kcmil
Conductor - Copper Str Size	250 kcmil
Range	
Conductor - Copper Str Size	250 kcmil

Configuration

Connector Type	Limiter
----------------	---------

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - B Length fraction	1 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.00 in
Dimension - Length Overall	16.25 in
inch	

General

Feature - Barrel Style	Tapered
Plated	Y
Insulation Type	Rubber
Die Index	16
UPC	781810000779
Insulation	Y
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810000779
UPC 14 Digit GTIN	00781810000779

Logistics

Minimum Pack Quantity	1
Pallet Quantity	384
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)