



LYS31C, Replaceable Link Limiter - Cable To Cable

By Burndy
Catalog # [LYS31C](#)



Limiter Replaceable Link, 350 KCMIL, Tin plated, 18 Index

Features

- Type LYS Replaceable Link Limiter incorporates the functions of both fuse and coupler
- For use with rubber and paper-insulated cable, it is designed to facilitate rapid replacement of Limiter Links upon clearing

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	350 kcmil
Conductor - AL Str Size Range	350 kcmil
Conductor - Copper Str Size	350 kcmil
Range	
Conductor - Copper Str Size	350 kcmil

Configuration

Connector Type	Limiter
----------------	---------

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - B Length fraction	1-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.25 in
Dimension - Length Overall	16.25 in
inch	

General

Feature - Barrel Style	Tapered
Plated	Y
Insulation Type	Rubber
Die Index	18
UPC	781810000823
Insulation	Y
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810000823
UPC 14 Digit GTIN	00781810000823

Logistics

Minimum Pack Quantity	1
Pallet Quantity	540
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)