



Manual Cable Cutter, up to 1000 kcmil CU/AL

By Burndy
Catalog # [MCC1000](#)

Manual Cable Cutter, Steel Blades, Cuts up to 1000 kcmil Copper & Aluminum Cables

Features

- High quality design and construction
- Rugged high quality steel blades
- Fiberglass handles with soft grips

Application

Cutting

Specifications

Standards - RoHS Compliance	EX
Status	
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Conductor

Crimping Ranges	• Cutting Capacity : Copper upto 1000 kcmil • Aluminum: upto 1000 kcmil
-----------------	---

Dimensions

Length	32 in
Weight	9 lb.

Height	2 in
Width	6 in
Cable Insulation Diameter	1.900 in
Maximum Dimensions	32 in x 6 in x 2 in

General

Application - For Use On	Aluminum, Copper Cable
Sub Brand	HYTOOL
Tool Type	Manual Cable Cutter
Product Type	Copper & Aluminum Cutter
UPC	781810174869
Type	Cutter
UPC 12 Digit	781810174869
UPC 14 Digit GTIN	00781810174869

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalog \[English\]](#)