



Manual Cable Cutter, up to 600 kcmil Copper and Aluminum

By Burndy
Catalog # **MCC600**

Manual Cable Cutter, 600 kcmil CU/AL



Features

- Rugged, high quality steel cutting blades
- Fiberglass handles with soft grips
- Excellent cutting edge performance
- Minimum of cable distortion

Application

Cutting

Specifications

Standards - RoHS Compliance EX
Status

Conductor

Crimping Ranges

- Cutting Capacity : Copper upto 600 kcmil
- Aluminum: upto 600 kcmil

Dimensions

Length 21 in

Cable Insulation Diameter	1.310 in
Maximum	
Width	5 in
Weight	3.5 lb.
Height	2 in
Dimensions	21 in x 5 in x 2 in

General

Application - For Use On	Aluminum, Copper Cable
Type	Cutter
UPC 12 Digit	781810566114
UPC 14 Digit GTIN	00781810566114
Tool Type	Manual Cable Cutter
UPC	781810566114

Logistics

Package Contents	Tool only
Minimum Pack Quantity	1

Product Assets

[Catalog \[English\]](#)

A Hubbell brand