



Crimper, Installs #14-4/0 AWG, O & D3 Grooves

By Burndy
Catalog # [MD68](#)

HYTOOL™ Hand-Operated Crimper, #14 AWG - 4/0 AWG, Perm O and D3 grooves



Features

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

- Crimping Ranges
- Copper: 10 sol. - 500 Kcmil
 - Copper Flex: #8 to 350 kcmil

Dimensions

Length 25.38 in
Weight 6 lb.
Height 2 in

Width 7.04 in
Dimensions 25.38 in x 7.04 in x 2 in

Force Related

Crimp Force Capacity 4.5 ton

General

Application - For Use On Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors

Trade Name HYTOOL™
Series HYTOOL™ Series
Tool Type Hand Operated Crimper
Product Type 4.5-Ton
Die Type W Die and X Die
UPC 781810446553
UPC 12 Digit 781810446553
UPC 14 Digit GTIN 00781810446553

Logistics

Package Contents Tool only

Product Assets

[Catalog \[English\]](#)