



MD6 Hotstick Tool, Forged Steel Jaws BG & D3, 60" Fiberglass Pole

By Burndy
Catalog # [MD6HS60](#)

HYTOOL™ 60" Hotstick #14-4/0, Perm BG/D3



Features

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Dimensions

Length 69 in
Weight 15.5 lb.

Force Related

Crimp Force Capacity 4.5 ton

General

Trade Name	HYTOOL™
Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Type	Crimper
UPC 12 Digit	781810446010
UPC 14 Digit GTIN	00781810446010
Tool Type	Hot Stick
UPC	781810446010
Die Type	W Die and X Die

Logistics

Package Contents Tool only
Minimum Pack Quantity 1

Product Assets

[Catalog \[English\]](#)