



HYTOOL™ Hand Operated Full Cycle Ratchet Crimper, Polymer Handles

By Burndy
Catalog # [MD734R](#)

Hand operated full cycle ratchet tool, Hytool, Handle material: Reinforced composite Polymer, Crimp Force: 9000 lbs.



Application

Crimping

General

Application - For Use On	Copper Terminals and Splices, Copper Battery Terminals, Thin-Wall C-Taps
Catalog Number	MD734R
Crimp Force Capacity	4.5 ton
Die Type	W and X Die
EU RoHS Indicator	Yes
Tool Type	Hand Operated Crimper
Trade Name	POSI-PRESS™ HYTOOL™
Type	Crimper
UPC	781810040430
UPC 12 Digit	7818100404300

Dimensions

Length	25 in
Weight	7 lb
Width	8 in

Conductor Related

Crimping Ranges	Copper Lugs/Splices #8 - 500 kcmil, Copper Lugs/Splices #8 - 350 kcmil Flex, Copper Battery Lugs #8 - 350 kcmil Flex, Thin Wall C-Taps #12 - 3/0 AWG
-----------------	--

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Package Contents	Tool only
------------------	-----------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_082_OTJF_MD734R_lineart](#)
[Sales Drawings - SE209552-01_A](#)



A proud member of the Hubbell Family.