



Full Cycle Ratchet Crimper, #22-10 AWG Nylon Insulated Terminals and Splices

By Burndy
Catalog # [MR18](#)



Full Cycle Ratchet Crimper, #22-10 AWG Nylon Insulated.

Features

- Permanent die sets
- Heavy duty forged steel frame
- Full cycle ratchet mechanism
- Emergency release
- Comfort grip handles

Application

Crimping

General

Application - For Use On	Nylon Insulated Terminals and Splices
Catalog Number	MR18
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810011201
UPC 12 Digit	7818100112011

Dimensions

Dimensions	8.88 in x 6.00 in x 2.50 in
Height	2.5 in
Length	8.88 in
Weight	1.1 lb
Width	6 in

Conductor Related

Crimping Ranges	#22 - #10 AWG
-----------------	---------------

Certifications And Compliance

Buy American Compliant	No
Standards - RoHS Compliance	EX
Status	

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Installation Manuals - MR15 MR18, MR20 Operating Manual](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_082_OTXF_MR15_MR18_MR20_lineart](#)
[Sales Drawings - 10113613](#)
[Specifications - MR18](#)