



Full Cycle Ratchet Crimper, Red #22-18  
AWG, Blue #18-14 AWG, Yellow #12-10  
AWG, YAE connectors

By Burndy  
Catalog # [MR8D94](#)

Full Cycle Ratchet, R/B/Y, #22-10, YAE

Features

- Fully enclosed, protected ratchet mechanism does not allow the handles to be opened until full ratchet cycle is completed
- Easy groove identification with color-coded dies
- Cast Aluminum body, other parts Alloy Steel

Application

Crimping

Specifications

Standards - RoHS Compliance    EX  
Status

Conductor

Crimping Ranges                      #22 - #10 AWG

Dimensions

Length                                      10.65 in

Height                                      1.39 in  
Width                                        3.31 in  
Dimensions                                10.65 in x 3.31 in x 1.39 in

General

Trade Name                                HYTOOL™  
Tool Type                                   Full Cycle Ratchet Crimper  
Die Type                                   Permanent Die Grooves  
UPC                                          781810029985  
Type                                          Crimper  
UPC 12 Digit                               781810029985  
UPC 14 Digit GTIN                       00781810029985

Logistics

Package Contents                        Tool only

Product Assets

[Catalog \[English\]](#)