



Dieless Crimper, #8 Str-4/0 Str CU Aircraft Cable

By Burndy
Catalog # MY28

Dieless Mechanical Crimper, HD Forged Steel, #8 Str - 4/0 Str CU Aircraft Cable

Features

- Easy to adjust nest die with knurled steel knob and machine hreads
- Rugged tool design with heavy duty forged steel with reinforced back and handles
- Bench mount adapter (sold separately) available
- 31" diameter hole for bench mounting operations

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Conductor

Crimping Ranges	#8 Str. - 4/0 Str.
-----------------	--------------------

Dimensions

Length	22.65 in
Weight	8 lb.

Height	1.12 in
Width	4.86 in
Dimensions	22.65 in x 4.86 in x 1.12 in

General

Application - For Use On	#8-4/0 AWG Copper Aircraft Cable (YAV-L, YSV-L)
Trade Name	HYTOOL™
Sub Brand	HYTOOL
Tool Type	Mechanical Dieless Crimper
Product Type	MY Series
Die Type	Dieless
UPC	781810461952
Finish Type	Black Matte
UPC 12 Digit	781810461952
UPC 14 Digit GTIN	00781810461952

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalog \[English\]](#)