



Dieless Mechanical Crimper, Heavy Duty Forged Steel, #8 Str - 2/0 Str. Copper aircraft cable (flexible)

By Burndy
Catalog # [MY286](#)

Dieless Crimper, #8 Str-2/0 Str CU Aircraft Cable (flexible).

Features

- Two-ply covered handles of MY29-3C and MY29-11C designs
- Heavy duty forged steel back body and handles
- Strong reinforced forged steel back
- Setting plate
- .31" diameter hole for bench mounting operations
- Comfort grips
- Extra strong heavy duty reinforced handles
- Indentor die
- Knurled steel adjusting knob

Application

Crimping

General

Application - For Use On	#8-2/0 AWG Copper Aircraft Cable Flex (YAE-L, YAEV-RS, YAEV-H, YAV-RH)
Catalog Number	MY286
Die Type	Dieless
Finish Type	Black Matte
Tool Type	Mechanical Dieless Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810461976
UPC 14 Digit GTIN	00781810461976

Dimensions

Dimensions	22.65 in x 4.86 in x 1.12 in
Height	1.12 in
Length	22.65 in
Weight	8 lb
Width	4.86 in

Conductor Related

Crimping Ranges	#8 Str. - 2/0 Str.
-----------------	--------------------

Certifications And Compliance

Standards - RoHS Compliance	EX
Status	

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_MY_LineArt](#)
- [Sales Drawings - sd026316-01](#)
- [Specifications - MY286](#)



A Hubbell brand