



MY2911 Kit with Dieless Tool, Case, and Select YA, YAV HYLUG™ Series Terminals

By Burndy
Catalog # [MY29UNIVERSALKIT](#)

MY2911 Dieless with YA, YAV HYLUG™, Case



Features

- Two-ply covered handles of MY29-3C and MY29-11C designs
- Heavy duty forged steel back body and handles
- Strong reinforced forged steel back
- Setting plate
- .31" diameter hole for bench mounting operations
- Comfort grips
- Extra strong heavy duty reinforced handles
- Indentor die
- Knurled steel adjusting knob

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

Crimping Ranges #8 Str. - 250 kcmil, 30 Navy -
250 Navy, #8 Str. - 4/0 Str

Dimensions

Length 23.38 in
Height 2.5 in
Width 10.31 in

Dimensions

23.38 in x 10.31 in x 2.5 in

General

Trade Name	HYTOOL™
Tool Type	Mechanical Dieless Crimper
Die Type	Dieless
UPC	781810033852
Type	Crimper
UPC 12 Digit	781810033852
UPC 14 Digit GTIN	00781810033852

Logistics

Package Contents	(1 each) MY2911, MY29KITCASE, (50 each) YA8CLBOX, YAV28LTC12FX, YAV25LTC38FX, YAV26LTC38FX, YA29LBOX, YAV2CLTC516FX, YAV27LTC12FX, YAV4CLTC516FX, YAV6CLTC14FX, YAV1CLTC38FX
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)