


Substation - Aluminum Bolted Terminal

By Burndy

Catalog # [NAR46A4N45](#)

Substation Connectors



Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	1
Conductor - Connection Combination	Cable to Flat
Conductor - AL Str Size	1250 kcmil 1272 kcmil 1300 kcmil 1351 kcmil 1400 kcmil 1431 kcmil 1500 kcmil 1590 kcmil 1600 kcmil
Conductor - AL Str Size Range	1250 kcmil-1600 kcmil
Conductor Type	- AL C Str-Size - ACSR C Str-Size
Conductor - ACSR Str Size	1113 (54/19) Finch kcmil 1192.5 (45/7) Bunting kcmil 1192.5 (54/19) Grackle kcmil 1272 (54/19) Pheasant kcmil 1351.5 (54/19) Martin kcmil 1431 (54/19) Plover kcmil
Conductor - ACSR Str Size Range	1113 (54/19) Finch kcmil-1431 (54/19) Plover kcmil

Configuration

Physical Attribute - Pad Orientation	45 Degree
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Physical Attribute - Pad Alignment	Offset

Physical Attribute - Number of Holes 4

Connector Type Terminal

Dimensions

Dimension - Pad Width inch	2.75 in
Package Height	0.000 in
Dimension - Height mm	93.7 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	3.69 in
Package Weight	0.000 lb.
Dimension - Width mm	94 mm
Dimension - Width inch	3.72 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	182 mm
Dimension - B Length inch	4.38 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	7.16 in

Force Related

Installation Torque Recommended in-lb 480 LBS/in

General

Plated	N
Material - Hardware	Aluminum
One Wrench Installation	Y
Clamping Element Design	Body And Cap
UPC	781810054222
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810054222
UPC 14 Digit GTIN	00781810054222

Logistics

Pallet Quantity 144
Carton Quantity 4



A Hubbell brand