



Cutting Die for use in 15-Ton, 1.2" max diameter

By Burndy
Catalog # [P15K](#)



15T Cutting Die, 1.2" Max Dia

Features

- Durable Steel Alloy Material
- Twin Cutter P Style
- Cutting Capacity: 1.2" max diameter

Application

Cutting

Specifications

Standards - RoHS Compliance Status	EX
EU RoHS Indicator	Yes

Force Related

Crimp Force Capacity	15 ton
----------------------	--------

General

Application - For Use On

- Maximum Cutting Diameter: 795 kcmil ACSR
- 750 kcmil Copper/Aluminum with 1.20" dia over Insulation
- 1.20" dia Bare Copper/Aluminum

Die Type

UPC

Type

UPC 12 Digit

UPC 14 Digit GTIN

P Die

781810008720

Die

781810008720

00781810008720

Logistics

Package Contents

Pallet Quantity

Carton Quantity

Die only

891

1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand