



PAT221 Battery Crimper, Dies/Wheels, #22-
#1 AWG, Hard Case, 2Ah Makita Batteries

By Burndy
Catalog # [PAT221A02A2](#)

PATRIOT® Series, PAT221 Small Terminal Battery Crimper for #22
AWG-#1 AWG, Hard Case, 2.0Ah Makita Batteries

Features

- Dies Included: (2) Dies: 2210B221, 2210NV221, (2) Die Wheels: 81WHL221, 122WHL221
- Scissor action head design
- One-second cycle time with auto retract and calibration
- Interchangeable crimping dies and wheels
- Connector hold feature for easy wire insertion
- LED Worklight
- Red LED to indicate an incomplete crimp
- Safety Trigger Lock and Emergency Release

Application

Crimping

Specifications

Buy American Compliant No

Conductor

Crimping Ranges Copper: #22 AWG - #1 AWG
terminals and splices

Current

Operating Voltage 18 VDC

Dimensions

Weight 2.6 lb.
Height 4.2 in
Width 2.8 in
Length 10.6 in



Dimensions 10.6 in x 2.8 in x 4.2 in

General

Tool Type Battery Actuated Crimper
Container Type Hard Case
Application - For Use On Copper Terminals, Splices
Die Type Interchangeable
UPC 621945665521
Trade Name PATRIOT®
Type Crimper
UPC 12 Digit 621945665521
Series PATRIOT® Series

Logistics

Package Contents Crimper, (2) Dies: 2210B221, 2210NV221, (2) Die Wheels: 81WHL221, 122WHL221, (2) 2.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case

Operational

Recharge Time 0.5 hr
Battery Type 2.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source 120V-AC Charger

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)