



PATRIOT® 11-Ton Dieless C-Head Battery Crimper, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case

By Burndy
Catalog # [PAT444SL5](#)

PAT444S 11T Dieless C-Head Battery Crimper, 5Ah Li-ion, AC, Hard Case.

Features

- C-Head for easy access and increased flexibility
- Dieless System with range taking capability
- #4 AWG -1000 kcmil Copper and Aluminum,#4 AWG - 556.5 kcmil ACSR, AAC, AAAC, ACAR
- 355° Head Rotation
- Ergonomically balanced

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT444SL5
Container Type	Hard Case
Crimp Force Capacity	11 ton
Die Type	Dieless
EU RoHS Indicator	Contact Manufacturer
Power Source	120V-AC Charger
Recharge Time	0.75 h
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945484351

Dimensions

Dimensions	16.90 in x 3.20 in x 13.70 in
------------	-------------------------------



Height	13.7 in
Length	16.9 in
Weight	14.8 lb
Width	3.2 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 kcmil; Aluminum: #4 AWG - 1000 kcmil; ACSR: #4 AWG - 556.5 kcmil
-----------------	---

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Product Assets

- [Brochures - PAT444S Series Brochure](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - BUR_PAT444S_trilingual](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50076051](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Specifications - PAT444SL5](#)
- [Video - The New PAT444S Dieless Tool](#)



A Hubbell brand