



11T Dieless C-Head Battery Crimper, Hard Case, No Batt/Chgr, Makita Power

By Burndy
Catalog # [PAT444SLCB](#)

PATRIOT® Series, 11-Ton Dieless C-Head Battery Crimper, Hard Case, No Batteries, Makita Power

Features

- C-Head for easy access and increased flexibility
- Dieless System with range taking capability
- #4 AWG -1000 kcmil Copper and Aluminum,#4 AWG - 556.5 kcmil ACSR, AAC, AAAC, ACAR
- 355° Head Rotation
- Ergonomically balanced

Application

Crimping

Conductor

Crimping Ranges	• Copper: #4 AWG - 1000 kcmil • Aluminum: #4 AWG - 1000 kcmil • ACSR: #4 AWG - 556.5 kcmil
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Weight	14.80 lb.
Height	16.9 in
Width	13.7 in
Length	3.2 in
Dimensions	3.2 in x 13.7 in x 16.9 in

Force Related

Crimp Force Capacity	11 ton
----------------------	--------

General

Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Die Type	Dieless
UPC	621945524873
Trade Name	PATRIOT®
Type	Crimper
UPC 12 Digit	621945524873
Series	PATRIOT® Series

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, Lanyard, Hard Case

Operational

Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	No Charger

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)