



11T Dieless C-Head Battery Crimper, Hard Case, 3Ah Makita Batteries

By Burndy
Catalog # [PAT444SLI](#)

PATRIOT® Series, 11-Ton Dieless C-Head Battery Crimper, Hard Case, 3.0Ah Makita Batteries

Features

- C-Head for easy access and increased flexibility
- Dieless System with range taking capability
- #4 AWG -1000 kcmil Copper and Aluminum,#4 AWG - 556.5 kcmil ACSR, AAC, AAAC, ACAR
- 355° Head Rotation
- Ergonomically balanced

Application

Crimping

Specifications

Buy American Compliant	No
EU RoHS Indicator	Contact Manufacturer

Conductor

- | | |
|-----------------|--|
| Crimping Ranges | <ul style="list-style-type: none">• Copper: #4 AWG - 1000 kcmil• Aluminum: #4 AWG - 1000 kcmil• ACSR: #4 AWG - 556.5 kcmil |
|-----------------|--|

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Length	16.9 in
Weight	14.80 lb.
Height	13.7 in
Width	3.2 in
Dimensions	16.9 in x 3.2 in x 13.7 in



Force Related

Crimp Force Capacity	11 ton
----------------------	--------

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Trade Name	PATRIOT®
Sub Brand	PATRIOT® CRIMPER
Series	PATRIOT® Series
Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Die Type	Dieless
UPC	621945474451
Type	Crimper
UPC 12 Digit	621945474451

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.5 hr
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)