



# PATRIOT® T3 Technology 11-Ton Dieless Battery Crimper, C-Head, Uncovered, No Batteries, No Charger, Hard Case

By Burndy  
Catalog # [PAT444ST3U0002](#)

PAT444ST3 Tech 11T Dieless Battery Crimper, C-Head, Uncovered, No Batteries, No Charger, Hard Case.

## Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments, photos, and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-Head for easy access and increased flexibility
- Dieless System with range taking capability
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

## Application

Crimping

## General

|                          |                                                                         |
|--------------------------|-------------------------------------------------------------------------|
| Application - For Use On | Copper, Aluminum, ACSR<br>Terminals and Splices, Cable<br>Pulling Heads |
| Battery Type             | No Batteries Included (Accepts<br>2.0Ah-6.0Ah Makita LI<br>Batteries)   |
| Catalog Number           | PAT444ST3U0002                                                          |
| Container Type           | Hard Case                                                               |
| Crimp Force Capacity     | 11 ton                                                                  |
| Die Type                 | Dieless                                                                 |
| Power Source             | No Charger                                                              |
| Tool Type                | Battery                                                                 |
| Type                     | Crimper                                                                 |
| UPC                      | 621945624610                                                            |



## Dimensions

|            |                              |
|------------|------------------------------|
| Dimensions | 14.95 in x 3.25 in x 16.9 in |
| Height     | 16.9 in                      |
| Length     | 14.95 in                     |
| Weight     | 15.2 lb                      |
| Width      | 3.25 in                      |

## Electrical Ratings

|                   |        |
|-------------------|--------|
| Operating Voltage | 18 VDC |
|-------------------|--------|

## Conductor Related

|                 |                                                                                                 |
|-----------------|-------------------------------------------------------------------------------------------------|
| Crimping Ranges | Copper: #4 AWG - 1000 kcmil;<br>Aluminum: #4 AWG - 1000<br>kcmil; ACSR: #4 AWG - 556.5<br>kcmil |
|-----------------|-------------------------------------------------------------------------------------------------|

## Logistics

|                  |                             |
|------------------|-----------------------------|
| Package Contents | Crimper, Lanyard, Hard Case |
|------------------|-----------------------------|

## Product Assets

[Brochures - T3 Technology Trifold Brochure](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - BUR\\_PAT444S\\_trilingual](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50108199](#)  
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)  
[Specifications - PAT444ST3U0002](#)  
[Video - BURNDY T3 APP Features and Benefits](#)  
[Video - Introducing the PAT444ST3](#)  
[Video - BURNDY T3 APP Install & Register](#)



A Hubbell brand