



T3 Tech 11T Dieless Battery Crimper, C-Head, Pro Bag, No Batt/Chgr, Makita Power

By Burndy
Catalog # PAT444ST3U0003

PATRIOT® Series, T3 Technology 11-Ton Dieless Battery Crimper, C-Head, Pro Bag, No Batteries, Makita Power



Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments, photos, and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-Head for easy access and increased flexibility
- Dieless System with range taking capability
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

Conductor

Crimping Ranges	• Copper: #4 AWG - 1000 kcmil • Aluminum: #4 AWG - 1000 kcmil • ACSR: #4 AWG - 556.5 kcmil
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Weight	15.20 lb.
Height	16.9 in
Width	3.25 in

Length	14.95 in
Dimensions	14.95 in x 3.25 in x 16.9 in

Force Related

Crimp Force Capacity	11 ton
----------------------	--------

General

Tool Type	Battery
Container Type	Nylon Pro Bag
Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Die Type	Dieless
UPC	621945625167
Type	Crimper
Series	PATRIOT® Series

Logistics

Pallet Quantity	12
Carton Quantity	1
Package Contents	Crimper, Lanyard, Nylon Pro Bag

Operational

Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	No Charger

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)