



15T Covered C-Head Battery Crimper, Hard Case, 5Ah Makita Batteries

By Burndy
Catalog # [PAT46CLWSL5](#)

PATRIOT® Series, 15-Ton Covered C-Head Battery Crimper, Hard Case, 5.0Ah Makita Batteries



Features

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, scoop style C-head with 355° head rotation
- Ergonomically balanced

Application

Crimping

Conductor

Crimping Ranges	• Copper: #14 AWG Str. - 1500 kcmil • Aluminum: #8 AWG - 1250 kcmil • Ground Rod: 1/2"-1" diameter
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Weight	18.95 lb.
Height	12.88 in
Width	3.26 in
Length	18.44 in
Jaw Width	2.00 in
Dimensions	18.44 in x 3.26 in x 12.88 in

Force Related

Crimp Force Capacity	15 ton
----------------------	--------

General

Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Die Type	P Die and U Die with PUADP1 Adapter
UPC	621945477728
Trade Name	PATRIOT®
Type	Crimper
UPC 12 Digit Series	621945477728 PATRIOT® Series

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.75 hr
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)