



15T Covered C-Head Battery Crimper, Hard Case, No Batt/Chgr, Makita Power

By Burndy
Catalog # [PAT46CLWSLILCB](#)

PATRIOT® Series, 15-Ton Covered C-Head Battery Crimper, Hard Case, No Batteries, Makita Power

Features

- 2 jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, scoop style C-head with 355 head rotation
- Ergonomically balanced

Application

Crimping

Conductor

Crimping Ranges	• Copper: #14 AWG - 1500 kcmil • Aluminum: #8 AWG - 1250 kcmil • Ground Rods: 1/2"-1" diameter
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions



Weight	31.20 lb.
Height	12.88 in
Width	3.26 in
Length	18.44 in
Dimensions	18.44 in x 3.26 in x 12.88 in

General

Tool Type	Battery Actuated Crimper
Die Type	P Dies and U Dies with PUADP1 Adapter
UPC	621945499003
Trade Name	PATRIOT®
Type	Crimper

Logistics

Minimum Pack Quantity	1
-----------------------	---

Operational

Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
--------------	---