



15T Latch Head Battery Crimper, Pro Bag, 5Ah Makita Batteries

By Burndy
Catalog # [PAT46LWL5PB](#)

PATRIOT® Series, 15-Ton Latch Head Battery Crimper, Pro Bag, 5.0Ah Makita Batteries



Features

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, "latch head" with 355° head rotation
- Ergonomically balanced

Application

Crimping

Specifications

Buy American Compliant	No
EU RoHS Indicator	Contact Manufacturer

Conductor

Crimping Ranges	• Copper: #14 AWG Str. - 1500 kcmil • Aluminum: #8 AWG - 1250 kcmil • Ground Rod: 1/2"-1" diameter
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Length	18.59 in
Weight	15.50 lb.
Height	13.93 in
Width	3.26 in
Jaw Width	2.00 in
Dimensions	18.59 in x 3.26 in x 13.93 in

Force Related

Crimp Force Capacity	15 ton
----------------------	--------

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Crimper
Container Type	Nylon Pro Bag
Die Type	P Die and U Die with PUADP1 Adapter
UPC	621945561489
Type	Crimper
UPC 12 Digit	621945561489

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12
Carton Quantity	1

Operational

Recharge Time	0.75 hr
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)