



**PATRIOT® 15-Ton Latch Head
Battery Actuated Crimper,
Hydraulic Self-Contained, No
Batteries, No Charger, Hard Case**

By Burndy
Catalog # [PAT46LWLILCB](#)

PAT46 15T Latch Head Battery Crimper, No Batteries, No
Charger, Hard Case.

Features

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, "latch head" with 355° head rotation
- Ergonomically balanced

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT46LWLILCB
Container Type	Hard Case
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Power Source	No Charger
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	781810654798
UPC 14 Digit GTIN	00781810654798

Dimensions

Dimension - Height mm	0 mm
Dimensions	18.59 in x 3.26 in x 13.93 in

Height	13.93 in
Jaw Width	2.00 in
Length	18.59 in
Weight	15.5 lb
Width	3.26 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter
-----------------	---

Certifications And Compliance

Standards - RoHS Compliance	UI
Status	

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, Lanyard, Hard Case

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50002858](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PAT46LWLILCB](#)



A Hubbell brand