



15T C-Head Battery Crimper, Hard Case, 5Ah Makita Batteries

By Burndy
Catalog # [PAT46LWSL5](#)

PATRIOT® Series, 15-Ton C-Head Battery Crimper, Hard Case, 5.0Ah Makita Batteries

Features

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, scoop style C-head with 355° head rotation
- Ergonomically balanced

Application

Crimping

Specifications

Buy American Compliant	No
EU RoHS Indicator	Under Review

Conductor

Crimping Ranges	• Copper: #14 AWG Str. - 1500 kcmil • Aluminum: #8 AWG - 1250 kcmil • Ground Rod: 1/2"-1" diameter
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Length	18.44 in
Weight	17.65 lb.
Height	12.88 in
Width	3.26 in
Jaw Width	2.00 in
Dimensions	18.44 in x 3.26 in x 12.88 in



Force Related

Crimp Force Capacity	15 ton
----------------------	--------

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Trade Name	PATRIOT®
Sub Brand	PATRIOT® CRIMPER
Series	PATRIOT® Series
Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Die Type	P Die and U Die with PUADP1 Adapter
UPC	621945470095
Type	Crimper
UPC 12 Digit	621945470095

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.75 hr
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)