



PATRIOT® 15-Ton C-Head Battery Actuated Crimper, Hydraulic Self-Contained, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Nylon Pro Bag

By Burndy
Catalog # [PAT46LWSL5PB](#)

PAT46 15T C-Head Battery Crimper, 5Ah Li-ion, AC, Nylon Pro Bag.



Features

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, scoop style C-head with 355° head rotation
- Ergonomically balanced

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT46LWSL5PB
Container Type	Nylon Pro Bag
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
EU RoHS Indicator	Under Review
Power Source	120V-AC Charger
Recharge Time	0.75 h
Sub Brand	PATRIOT® Crimper
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945561649

Dimensions

Dimensions	18.44 in x 3.26 in x 12.88 in
Height	12.88 in
Jaw Width	2.00 in
Length	18.44 in
Weight	17.65 lb
Width	3.26 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter
-----------------	---

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50106125](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PAT46LWSL5PB](#)



A Hubbell brand