



PATRIOT® Series, 15-Ton C-Head Battery Actuated Crimper, Hydraulic Self-Contained, (2) 3.0Ah 18V Li-ion Batteries, 12V-DC Charger, Hard Case

By Burndy
Catalog # PAT46LWSLIDC

15T C-Head, 3Ah, DC, Hard Case

Features

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, scoop style C-head with 355° head rotation
- Ergonomically balanced

Application

Crimping

Specifications

Standards - RoHS Compliance UI
Status

Conductor

- Crimping Ranges
- Copper: #14 AWG Str. - 1500 kcmil
 - Aluminum: #8 AWG - 1250 kcmil
 - Ground Rod: 1/2"-1" diameter

Dimensions

Dimension - Height mm	0 mm
Length	18.44 in
Weight	17.65 lb.
Height	12.88 in
Width	3.26 in
Jaw Width	2.00 in
Dimensions	18.44 in x 3.26 in x 12.88 in



Force Related

Crimp Force Capacity 15 ton

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Die Type	P Die and U Die with PUADP1 Adapter
UPC	781810672419
Type	Crimper
UPC 12 Digit	781810672419
UPC 14 Digit GTIN	00781810672419

Logistics

Package Contents
Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.5 hr
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	12V-DC Charger

Product Assets

[Catalog \[English\]](#)