



T3 Tech 15T Battery Crimper, Latch Head, Pro Bag, No Batt/Chgr, Makita Power

By Burndy
Catalog # [PAT46T3LU0003](#)

PATRIOT® Series, T3 Technology 15-Ton Battery Crimper, Latch Head, Pro Bag, No Batteries, Makita Power

Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- Light weight, latch head with 355° head rotation
- Uses P Dies and U Dies with PUADP1 Adapter
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

Conductor

Crimping Ranges	• Copper: #14 AWG Str. - 1500 kcmil • Aluminum: #8 AWG - 1250 kcmil • Ground Rod: 1/2"-1" diameter
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Weight	16.00 lb.
Height	15.18 in
Width	3.26 in



Length	18.59 in
Dimensions	18.59 in x 3.26 in x 15.18 in

Force Related

Crimp Force Capacity	15 ton
----------------------	--------

General

Tool Type	Battery Actuated Crimper, T3 Technology
Container Type	Nylon Pro Bag
Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Die Type	P Die and U Die with PUADP1 Adapter
UPC	621945625464
Type	Crimper
Sub Brand	PATRIOT®
Series	PATRIOT® Series

Logistics

Pallet Quantity	12
Carton Quantity	1
Package Contents	Crimper, Lanyard, Nylon Pro Bag

Operational

Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	No Charger

Product Assets

[Catalog \[English\]](#)



A Hubbell brand