



PATRIOT® Series, T3 Technology 15-Ton Battery Crimper, C-Head, Rubber Covered, two 3.0Ah 18V Li-Ion Batteries, 12V-DC Charger, Hard Case

By Burndy
Catalog # PAT46T3SC03D2

T3 Tech 15-Ton C-Head, Cvrdr, 3Ah, DC, HC

Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-head with 2" jaw opening with 355° head rotation
- Uses P Dies and U Dies with PUADP1 Adapter
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

Conductor

- Crimping Ranges
- Copper: #14 AWG Str. - 1500 kcmil
 - Aluminum: #8 AWG - 1250 kcmil
 - Ground Rod: 1/2"-1" diameter

Current

Operating Voltage18 VDC

Dimensions

Weight19.45 lb.
Height14.13 in



Width3.26 in
Length18.44 in
Dimensions18.44 in x 3.26 in x 14.13 in

Force Related

Crimp Force Capacity15 ton

General

Tool TypeBattery Actuated Crimper, T3 Technology
Container TypeHard Case
Application - For Use OnCopper, Aluminum, ACSR Terminals and Splices
Die TypeP Die and U Die with PUADP1 Adapter
UPC621945625600
TypeCrimper
Sub BrandPATRIOT®
SeriesPATRIOT® Series

Logistics

Package ContentsCrimper, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Battery Type3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source12V-DC Charger

Product Assets

[Catalog \[English\]](#)