



4-POINT 6T Dieless C-Head Battery Crimper, Pro Bag, 5Ah Makita Batteries

By Burndy
Catalog # [PAT4PC834L5PB](#)

PATRIOT® 4-POINT® Series, 6-Ton Dieless C-Head Battery
Crimper, Pro Bag, 5.0Ah Makita Batteries

Features

- Dieless System with range taking capabilities
- 360° head rotation
- 1.06" Jaw opening
- Overmolded handle for comfort and improved grip
- Ergonomically balanced

Application

Crimping

Specifications

Buy American Compliant	No
EU RoHS Indicator	Under Review
UL Listed	No

Conductor

Crimping Ranges	Copper Terminals: #8-1000 kcmil
	Copper Splices: #8-500 kcmil
	Copper Flex Terminals: #8-777.7 Flex
	Copper Flex Splices: #8-500 kcmil
	Aluminum Terminals: #8-750 kcmil
	Aluminum Splices: #8-350 kcmil*
	*1.06" barrel diameter maximum for aluminum splices due to jaw opening
	Aluminum HYPLUG™: #8-750 kcmil

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions



Length	15.62 in
Weight	12.50 lb.
Height	14.1 in
Width	3.25 in
Dimensions	15.62 in x 3.25 in x 14.1 in

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Application - For Use On	Copper, Aluminum Terminals and Splices, HYPLUG™
Trade Name	PATRIOT® 4-POINT®
Series	PATRIOT® 4-POINT® Series
Tool Type	Battery Actuated Crimper
Container Type	Nylon Pro Bag
Die Type	Dieless
UPC	621945561953
Type	Crimper
UPC 12 Digit	621945561953

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12
Carton Quantity	1

Operational

Recharge Time	0.75 hr
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)