



4-POINT 6T Dieless C-Head Battery Crimper, Hard Case, 3Ah Makita Batteries

By Burndy
Catalog # [PAT4PC834LI](#)

PATRIOT® 4-POINT® Series, 6-Ton Dieless C-Head Battery Crimper, Hard Case, 3.0Ah Makita Batteries

Features

- Dieless System with range taking capabilities
- 360° head rotation
- 1.06" Jaw opening
- Overmolded handle for comfort and improved grip
- Ergonomically balanced

Application

Crimping

Specifications

Standards - RoHS Compliance Status	EX
Buy American Compliant	No
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	Copper Terminals: #8-1000 kcmil Copper Splices: #8-500 kcmil Copper Flex Terminals: #8-777.7 Flex Copper Flex Splices: #8-500 kcmil Aluminum Terminals: #8-750 kcmil Aluminum Splices: #8-350 kcmil* *1.06" barrel diameter maximum for aluminum splices due to jaw opening Aluminum HYPLUG™: #8-750 kcmil
-----------------	---

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions



Dimension - Height mm	353.1 mm
Length	15.6 in
Weight	12.50 lb.
Height	14.1 in
Width	3.2 in
Dimensions	15.6 in x 3.2 in x 14.1 in

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Application - For Use On	Copper, Aluminum Terminals and Splices, HYPLUG™
Trade Name	PATRIOT® 4-POINT®
Sub Brand	PATRIOT® CRIMPER
Series	PATRIOT® 4-POINT® Series
Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Die Type	Dieless
UPC	781810505441
Type	Crimper
UPC 12 Digit	781810505441
UPC 14 Digit GTIN	00781810505441

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.5 hr
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)